

search :

Email :  Password :

**PAN PACIFIC**

[Home](#) [Services](#) [Products](#) [Distributors/Reps](#) [About us](#) [Contact Us](#)

home » products »

### Our Products

[AUDIO / VIDEO COMPONENTS & ACCESSORIES](#)

[VOICE / DATA COMPONENTS & ACCESSORIES](#)

[RF CONNECTORS & ADAPTORS](#)

[PC / APPLE AUDIO / VIDEO CABLES & ACCESSORIES](#)

[CONNECTORS & COMPONENTS](#)

[POWER STRIP](#)

[SECURITY](#)

[HAND TOOLS](#)



#### Molded Boot Snagless Cord

Meets ISO/IEC 11801, EIA/TIA 568-B.2-1 Cat 6 standard verified. All RJ45 plugs used are UL listed with 50u" gold plated contacts. 568B wiring unless specified.

Cat 6 performance specification to 250Mhz. Tested to 500Mhz.

4 Pair 24AWG stranded, polyolefin insulation, twisted pairs, no rip-cord, pvc jacket.

Molded strain relief to ensure the best performance.

Custom color and length available upon request.

1000 ft/roll Bulk Wire also available.

Short body staggered plugs.

SKU: **DC-568P-10BKMB**

Color: **Black**

#### Details

Black

10 ft.