DVI & D - SUB CONNECTORS

SOLDER TYPE, ZINC PLATED

- · Gold Plated Contacts
- White Plastic Fillings

Male **Female** DS-(XX)P DS-(XX)S

XX= Pins: 9, 15, 19, 23, 25, 37, 50.





MACHINE PIN SOLDER TYPE ZINC PLATED

- · Gold Plated Contacts
- White Platic Fillings
- Solder Cup with Machine Pin

Built with Machine Type Pin

Male

DS-(XX)P-MCH

Female

DS-(XX)S-MCH

XX= Pins: 9, 15, 25, 37.



SOLDER TYPE, TIN PLATED

- · All Plugs with Grounding Indents on Shells
- Gold Plated Contacts
- White Plastic Fillings
- All Tin Plated Shell

Male **Female** DS-(XX)S/T DS-(XX)P/T

XX= Pins: 9, 15, 19, 23, 25, 37, 50.



CRIMP HOUSING, ZINC PLATED

· Black Plastic Fillings

Male **Female**

DH-(XX)HP DH-(XX)HS

XX= Pins: 9, 15, 25, 37.



DVI SOLDER TYPE

Analog

DVI-17M Male, 17C

Digital

DVI-19M Single Link

DVI-25M Dual Link

Digital/Analog

DVI-23M Male, 23C DVI-29M Male, 23C

DVI-25F Female, 25C DVI-29F Female, 29C



CRIMP HOUSING, TIN PLATED

- · All Plugs w/ Grounding Indents on Shells
- Black Plastic Fillings

Male **Female**

DH-(XX)HS/T DH-(XX)HP/T

XX= Pins: 9, 15, 25, 37, 50.




CRIMP HOUSING, TIN PLATED

- · All Plugs w/ Grounding Indents on Shells
- UL-LISTED
- Black Plastic Fillings

Male DH-09HP/T-UL DH-25HP/T-UL

Female DH-09HS/T-UL

DH-25HS/T-UL



DH-25HS/T-UL

HIGH DENSITY, SOLDER TYPE

- · All Tin Plated Shells
- · All Plugs w/ Grounding Indents on Shells
- · Gold Plated Contacts
- White Plastic Fillings

Male **Female** DHS-(XX)P





XX= Pins: 15, 26, 44, 62, 78.

CRIMP HOUSING HIGH DENSITY

DHD-44HS

- · All Tin Plated Shells
- · All Plugs w/ Grounding Indents on Shells
- · All Pins Gold Plated
- Black Plastic Fillings

Male **Female** DHD-(XX)HP DHD-(XX)HS DHD-44HP

XX= Pins: 15, 26, 44, 62, 78.



See Pg 105 for Hood Used on the Connector