



MATERIALS:

Connector: 1st End – Standard Banana Plug

Spring – Beryllium Copper Alloy 172, Cond. HT.

Plug Body – Brass Alloy 360, 1/2 Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches

Insulation: Kraton. Color: Black

Coiled Cord: Coiled tinsel cord, 2 bundles, 7 strands silver, vinyl jacket 2.54 (.100) O.D.

Connector: 2nd End – 3.18 (1/8) Snap Receptacle - Brass

Finish: Nickel plated

Insulation: Kraton. Color; Black

Molded-In Resistor: 1 megohm \pm 10%, 1/4 Watt, Carbon Film

RATINGS:

Operating Temperature: +50°C. (+122°F.) Max.

ORDERING INFORMATION: Model 5534

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA