



FEATURES:

- Provides cross hole for cross stacking, and a jack for vertical stacking.
- Allows an Alligator Clip with leads to be used from a Banana Jack.

MATERIALS:

Conn: Insulated Minigator Clip

Material: Steel.

Finish: Nickel plated.

Insulator: Vinyl.

Color: Matches color of wire.

Conn: Banana Plug

Material: Spring, Beryllium Copper per QQ-C-533, Alloy 172, Cond. HT. Plug Body, Brass per QQ-B-626, Alloy 360, 1/2 Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire. Color: Matches color of wire.

Marking: "POMONA 3220-XX"

RATINGS:

Operating Temperature: +50° C. (+122° F.) Max.

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 3220-XX-*

XX = Cable Lengths, Standard Lengths: 4" (102), 12" (305), 18" (475), 24" (610), 36" (914), 48" (1219) & 60" (1524). Additional lengths can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: 3220-60-2 Indicates 60" in length, color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA