



MATERIALS:

Connector:

Body: Tarnish Resistant Plating, Center Contact: Gold Plated Beryllium Copper

Shielded Housing: Die cast aluminum, Alloy A380 or A384

Cover: .040 thick aluminum alloy 1100-H14

Screws: Steel. 4 each 2-32 x 1/4" pan head, self-tapping

Finish:

Shielded Housing – None

Cover – Clear anodized

Screws – Zinc per ASTM B633-85, Type II (bright blue)

RATINGS:

Operating Temperature: -55°C to +150°C

ORDERING INFORMATION: Model 3754

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA