



conductor: 26AWG (0.16mm*7c), TC wire
 drain wire: 26AWG (0.16mm*7c), TC wire
 braid: 0.12mm*128#, Mg+Al wire
 insulation: PP, OD:1.3MM
 insulation: Al foil, width:30MM, thick:0.025MM, 100%
 insulation: Al foil, width:10MM, thick:0.025MM, 100%
 MYLAR, the width:11MM
 drain wire: 26AWG(0.16mm*7c), TC wire
 insulation: PP, OD: 0.70MM
 jacket: PVC, OD:8.5mm, black color
 conductor: 26AWG (0.16*7c), TC wire
 the two wire must be twisted

the color:
 P1: white + blue
 P2: white + green
 P3: white + red
 P4: white + orange
 1: red
 2: yellow
 3: purple
 4: green
 5: white
 6: grey
 7: orange

Electric character:	
---------------------	--

conductor resistance	MAX. 146OHMS/KM AT 20C
----------------------	------------------------

insulation resistance	MIN. 100 MEGA OHMS-KM AT 20C
-----------------------	------------------------------

dielectric test	500VAC/MIN; NO BREAKDOWN
-----------------	--------------------------

impedance	100±100OHMS
-----------	-------------

delay	151PS/CABLE
-------	-------------

attenuation	FREQUENCY (MHZ) Attenuation(MAX.) DB/CABLE
-------------	---

	300KHZ-825MHZ	-8dB
--	---------------	------

	825MHZ-2475MHZ	-21dB
--	----------------	-------

	2475MHZ-4125MHZ	-30dB
--	-----------------	-------

REMARK

1. Available length: 30', 50'



		DESCRIPTION	HDMI CABLE, 26AWG	
		PART NO	HDI-1330/HDI-1350	
DRAW	JACKY	CONSUMER		
CHECK		DATE	2008/05/15	REV.
APP.		SHEET	1/1	UNIT mm SCALE 1:1