



- The color :
- P1: white + blue
 - P2: white + green
 - P3: white + red
 - P4: white + orange
 - 1: red
 - 2: yellow
 - 3: purple
 - 4: green
 - 5: white
 - 6: grey
 - 7: orange

REMARK:

The available length: 3', 6', 10', 12', 15', 25'



Electric character:	
conductor resistance	MAX. 237OHMS/KM AT 20C
insulation resistance:	MIN. 100 MEGA OHMS-KM AT 20C
dielectric test	500VAC/MIN; NO BREAKDOWN
impedance	100±100HMS
delay	5.05NS/M
Intra-skew	15IPS/CABLE
attenuation	FREQUENCY (MHZ) Attenuation(MAX.) dB/CABLE
	300KHZ-825MHZ -8dB
	825MHZ-2475MHZ -21dB
	2475MHZ-4125MHZ -30dB

		DESCRIPTION	HDMI CABLE, 28AWG
		PART NO	HDI-13XX
DRAW	JACKY	CONSUMER	
CHECK		DATE	2008/05/15
APP.		SHEET	1/1
		UNIT	mm
		SCALE	1:1