



- 1.REMARK:RG-58U CABLE  
 INNER CONDUCTOR:16X0.20mm CCS  
 DIELECTRIC:PE-OD:2.95mm  
 BRAID:32X0.12mm  
 JACKET:BLACK PVC OD4.95mm  
 2.RG-58U 500HM COAXIABLE CABLE

RG-58U



NBC-1503