

Quest now offers a broad range of bulk data and voice grade cables. New in our line is 4 pair Category 5e 350MHz solid and stranded and CAT6 solid in 1,000-foot pull boxes. These are high quality, UL listed and meet ANSI/TIA/EIA, ISO/IEC standards and offered in various colors. In addition, Quest also offers voice grade cable in flat silver satin and round in 1,000-foot reels.

BULK DATA CABLE

CATEGORY 5E BULK CABLE

4 PAIR 24AWG CAT5E 350MHz UTP CABLE
1,000 FT. PULL BOXES

SOLID

STRANDED

COLOR	ITEM #	COLOR	ITEM #
GRAY	NBW-1059	GRAY	NBW-1159
BLUE	NBW-1052	BLUE	NBW-1152
YELLOW	NBW-1055	YELLOW	NBW-1155
RED	NBW-1053	RED	NBW-1153
GREEN	NBW-1056	GREEN	NBW-1156
BLACK	NBW-1051	BLACK	NBW-1151
WHITE	NBW-1058	WHITE	NBW-1158

CATEGORY 6 BULK CABLE

4 PAIR 23AWG CAT6 SOLID UTP CABLE
1,000 FT. PULL BOXES

COLOR	ITEM #	COLOR	ITEM #
GRAY	NBW-1069	BLUE	NBW-1062

VOICE GRADE CABLE

ITEM #	DESCRIPTION
NBW-1426	2PR. (4C) 24AWG ROUND SOLID TEL. CABLE - 1,000'
NBW-1626	3PR. (6C) 24AWG ROUND SOLID TEL. CABLE - 1,000'
NBW-1826	4PR. (8C) 24AWG ROUND SOLID TEL. CABLE - 1,000'
NBW-2428	4C. 28AWG FLAT SILVER SATIN TEL. CABLE - 1,000'
NBW-2628	6C 28AWG FLAT SILVER SATIN TEL CABLE - 1,000'
NBW-2828	2PR. (4C) 24AWG ROUND SOLID TEL. CABLE - 1,000'

Please see Quest Full Line Catalog #Q700 for complete interconnect products



CAT5e 350MHz UTP Solid / Stranded UTP

- Meets Category 5e requirements as per ANSI/TIA/EIA, ISO/IEC standards
- 2nd Edition ISO/IEC 11801 CAT5e
- Excellent ACR values for Power Sum NEXT/ELFEXT attenuation and return loss
- UL Listed Type CM/CMR
- PVC Jacket
- 350MHz Rated Cable
- 4 pair 24AWG Solid or Stranded Copper
- 1,000 Foot Pull-boxes



CAT 6 FUTURELAN 250 Solid UTP

- In compliance with Proposed Category 6 requirements as per ANSI/TIA/EIA, ISO/IEC standards
- Positive ACR @ 250Mhz
- UL Listed Type CM / CMR
- PVC Jacket
- Star insert separator design
- 4 pair 23AWG Solid Copper
- 1,000 Foot Pull-boxes

