


[English](#) [日本語](#)
Electronics
a vital part of your world
**Find
Answers:**

Sunday, 9 October, 2005

CATALOG

 → [Cross Reference](#)
[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

 → [Part Number Search](#)

 → [Document Search](#)

 → [Product Type Search](#)

 → [Product Family Search](#)

 → [Alphabetical Search](#)

 → [RoHS/ELV Compliance & Alternates](#)

 → [CAD Model Search](#)

 → [Brand Search](#)

 → [Tool Search](#)

 → [Multiple Part Comparison](#)

 → [Lead Free Solutions](#)

 → [Help/Glossary](#)
[Home](#)

 e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Solder Sleeve Terminators
↳ Wire Terminators
Raychem CWT-1503  [Active](#)
[Not ELV or RoHS Compliant](#)
(Corporate P/N: 281949-000)
[Search for Compliant \(RoHS/ELV\)](#)
[Alternates](#)
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ↳ General Info ↳ Sales Info 	<ul style="list-style-type: none"> ↳ Pricing ↳ Product Availability 	<ul style="list-style-type: none"> ↳ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product View](#)
Searchable Features:

Brand:	Raychem
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Not relevant for lead free process
Terminal Type:	Pin, Post, Tab
Operating Temperature (Max.) (°C):	125
Wire Size to Pin/Post (mm² [AWG]):	0.61 [20], 0.61 – 0.95 [18 – 20], 0.24 – 0.38 [22 – 24]

Other Properties:

Connection Type:	Solder
Application Type:	Wire termination to pin/post/tab

Wire Size to Tab (mm² [AWG]):	0.24 – 0.95 [18 – 24]
Pin/Post Width (mm [in]):	0.89 – 1.14 [0.035 – 0.045], 1.14 – 1.52 [0.045 – 0.060]
Tab Width (mm [in]):	1.77 – 2.79 [0.07 – 0.11]
Tape Carrier:	No

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]