Innovation

Industries

Products



Support Center

Home > Products > Tubing & Harnessing > Product Feature Selector > Product Details


Molded Part Lip = With Lip

Operating Temperature = -75 - 150 °C

Resources

About TE

## 224W201-25/225-0 Product Details



My Account

## Features Documents Compliance Please Note: Use the Product Drawing for all design activity **Product Type Features** Molded Part Type 2 Molded Boot Molded Part Shape 90° Molded Part Lip With Lip Angle 90° Unicure Pre-Coated Epoxy Adhesive Description Adhesive Size 01 **Family Name** 224W2 Color Black Mechanical Attachment Adhesive Pre-Coating Dimensions Cable Diameter Range 5.20 - 11.00 [0.200 -(mm [in]) 0.430]Expanded ID, Min. (mm 11.00 [0.430] [in]) Recovered ID, Max. 5.20 [0.200] (mm [in]) **Body Features** Fluid Resistant Modified Material Elastomer **Housing Features** Material Systems Code

<b>Configuration Features</b>	
Material Code	25
Industry Standards	
Government/Industry Qualification	No
Approved Standards	VG95343 Parts 6,7,8 and 9
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes ?	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant
Environmental	
Operating Temperature (°C)	-75 - +150
Operation/Application	
Application	General Purpose
Purchasing Information	1
Adhesive Code	225
Other	
Brand	Raychem

Related Products
Not quite the product
you're looking for?
Find Similar Products
View Part in Product Feature Selector

Corporate Information

of Part (mm [in])

Max. Inside Diameter

Investors News Room Supplier Portal

About TE

Careers Terms & Conditions

Privacy Policy

Global Accessibility Statement

Quick Links

5.20 [0.200]

Distributor Inventory Product Cross Reference Documents & Drawings Product Compliance Support Center Site Map

Customer Support

Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account

Keep Me Informed









