




44A0111-20-8-MX Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

Spec 44, Spec 55 and Spec RCW Wire and Cable

44A0111-20-8

44A0111-20-8-MX ✔

TE Internal Number: 282028-013

Product Highlights [View All](#)

- Cable Type = Spec 44
- Wire Source = United States
- Cable Style = Primary
- Wire Size (AWG/CM) = 20 AWG
- Voltage Rating = 600 VAC

- [Pricing & Availability](#) >
- [Request Sample](#) >
- [Add to My Part List](#) +
- [Buy Product through Distributor](#) >

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features		Industry Standards	
Cable Type [?]	Spec 44	Government/Industry Qualification	No
Cable Style [?]	Primary	RoHS/ELV Compliance [?]	RoHS compliant, ELV compliant
Electrical Characteristics		Lead Free Solder Processes [?]	Not relevant for lead free process
Voltage Rating (VAC)	600	RoHS/ELV Compliance History	Always was RoHS compliant
Dimensions		Conditions for Usage	
Conductor Outer Diameter (mm [in])	1.01 [0.040]	Temperature Range (°C)	-65 - +150
Body Features		Wire Size - Details	20 AWG 0.62 mm ² , 0.00095 in ² , 19 x 32 AWG
Wire Size (AWG/CM)	20 AWG	Operation/Application	
Conductor Type	Tin-Coated Copper	Application	General Purpose - Light Weight
Wire Color	Gray	Packaging Features	
Nominal Outside Diameter (mm [in])	1.40 [0.055]	Wire Source	United States
Wire Diameter (mm [in])	1.40 [0.055]	Other	
Configuration Features		Brand	Raychem
Number of Conductors	1	Node Classification	Hook Up Wire

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)