

HOOK UP WIRE



✓ Active

TE CONNECTIVITY (TE)
44A0111-18-2

Raychem | SP

44A0111-18-2

TE Internal Number: 2820123007 Alias ID: 3-1192092-2

EU RoHS Compliant
EU ELV Compliant

Cable Type Spec 44
Voltage Rating (V) 600

Insulation Material Radiation-Crosslinked, Extruded Polyalkene

Conductor Material Tin-Plated Copper

Wire Size (AWG) 18



PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

WIRE, ELECTRIC, RADIATION-CROSSLINKED, TIN-COATED COPPER, LIGHTWEIGHT, GENERAL PURPOSE, 600 VOLT

PDF (TIFF AVAILABLE)

English

FEATURES



Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features Cable Type Spec 44 Product Classification Cable - High Performance - Spec 44, 55 & RCW Product Type Cable Cable Style Primary	
Configuration Features	
Number of Strands 19 Number of Conductors 1	
Electrical Characteristics	
Voltage Rating (V) 600	
Body Features	
Insulation Material Radiation-Crosslinked, Extruded Polyalkene Conductor Material Tin-Plated Copper Wire Color Red	
Dimensions	
Strand Size (AWG) 30 Wire Size (AWG) 18	
Wire Size (mm²) .82	
Conductor Diameter 1.27 mm [.05 in] Wire Diameter 1.65 mm [.065 in]	
Overall Outside Diameter 1.65 mm [.065 in]	
Usage Conditions	
Operating Temperature Range (°C) -65 – 150	
Other	
Wire Source United Kingdom	
PRODUCT COMPLIANCE -	+
Statement of Compliance	
Statement of Compliance	
Statement of Compliance PDF	