


D-609-07 Product Details

[Live Product Chat](#)



D-609-07

TE Part Number: 680327-000

Active

[Add to Part List](#)

Splices - Closed Barrel

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Splice
- Not Sealed
- Splice Type = Butt
- Butt Splice Type = Standard
- Body Style = DuraSeal

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [Color Coded Crimp Splicer, In-line, Tin Plated](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Splice
- [Sealed](#) = No
- [Splice Type](#) = Butt
- Body Style = DuraSeal
- [Insulation](#) = No
- Material = Copper Alloy
- [Finish](#) = Tin
- Color = None
- Connection Type = Crimp

Mechanical Attachment:

- Inside Diameter (mm [in]) = 1.75 [0.069]
- Ring Color = Blue

Body Related Features:

- [Butt Splice Type](#) = Standard
- [Wire Range \(mm \[AWG\]\)](#) = 0.50-1.40² [20-16]
- [Wire Range \(CMA\)](#) = 779 - 2,680

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application Type = Wire to wire splicing

Packaging Related Features:

- [Packaging Method](#) = Loose Piece

Other:

- Brand = Raychem