



HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY (TE) XFFR-20X25

Raychem | XFFR

CB5442-000

TE Internal Number: CB5442-000

EU RoHS Compliant

EU ELV Compliant

Wall Type Single

Resistant To Abrasion, Fluids, Mechanical Damage, Weathering

Low Outgassing No

Product Source US

Packaging Method Piece

DOCUMENTATION

Catalog Pages/Data Sheets

XFFR Pages From 9-1773447-9

PDF

English

At-Application-Tooling-For-Raychem-Heat-Shrink-Product-2-1773452-8

PDF

English

Product Specifications

Product Specification

Raychem XFFR Zero Halogen Heat Shrinkable Tubing

PDF

English

Instruction Sheets

Global Dimensional Life For RAYCHEM Heat Shrink Tubing Standard Size Products (Customer Distribution)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Wall Type Single

Body Features

Shrink Ratio 3:1

Color Black

Flexibility Semi-Rigid

Material Irradiated Modified Polyolefin

Fluid Type Brake Fluid, Water

Dimensions

Recovered Inside Diameter (Max) 19.1 mm [.752 in]

Usage Conditions

Shrink Temperature (Min) (°C) 70

Resistant To Abrasion, Fluids, Mechanical Damage, Weathering

Recovery Temperature (°C) 121

Flammability Flame-Retardant

Fluid Resistance Immersion Protection, Moisture/Spray Protection

Product Availability

Applicable Region Global

Packaging Features

Packaging Method Piece

Other

Low Outgassing No

Product Source US

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF

