


CWT-9004 Product Details



CWT-9004

Raychem Part Number:
691091-000

[Active](#)

SolderSleeve Wire Splices

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Sealing = Splash proof
- CMA (Min.-Max) = 4,800 - 9,000 CMA
- Wire Temperature Rating Range (Max.) = 85°C to 125°C

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SolderSleeve One-Step Wire Terminator, Low Temperature](#) (PDF, English)

Catalog Pages/Data Sheets:

- [Wire and Cable, Harnessing and Protection Products](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Connection Type = Solder

Housing Related Features:

- Sealing = Splash proof
- CMA (Min.-Max) (CMA [mm²]) = 4,800 - 9,000 [2.40 - 4.50]

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Wire Temperature Rating Range (Max.) = 85°C to 125°C
- Operating Temperature (Max.) (°C) = 125

Operation/Application:

- Application = Wire to Wire Splicing

Other:

- Brand = Raychem