




HARNESSING

HEAT SHRINK BOOTS



✓ Active

TE CONNECTIVITY (TE)

202D121-25/225-0

Raychem | CAP , CRPS

202D121-25/225-0

TE Internal Number: 402297-000

Alias ID: 1-1193037-9

EU RoHS Compliant

EU ELV Compliant

Lipped Yes

Operating Temperature Range (°C) -75 – 150

Adhesive Options None

Material Systems Code 25

Adhesive Pre-Coat Yes

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

Boot, Straight, With Lips

PDF

English

Product Environmental Compliance

Safety Data Sheet

Unicure 225 Adhesive

PDF

English

Unicure 225 Adhesive

PDF

French

Unicure 225 Adhesive

PDF

German

Unicure 225 Adhesive

PDF

Italian

Unicure 225 Adhesive

PDF

Spanish

Unicure 225 Adhesive

PDF

Swedish

Unicure 225 Adhesive

PDF

Dutch

Unicure 225 Adhesive

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

EPS Heat Shrinkable Polymeric Products

PDF

Dutch



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped Yes

Body Features

Material Systems Code 25

Adhesive Pre-Coat Yes

Material Modified Elastomer

Dimensions

Inside Diameter as Supplied 23.4 mm [.92 in]

Usage Conditions

Operating Temperature Range (°C) -75 – 150

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No

Approved Standards VG95343 Parts 6,7,8 and 9

Other

Adhesive Options None

Adhesive Type Unicure Pre-Coated Epoxy Adhesive

Statement of Compliance

Statement of Compliance

PDF
