



[+ TERMINALS & SPLICES](#)

SPLICES



✓ Active

TE CONNECTIVITY (TE)

D-110-35

Raychem

625159-000

TE Internal Number: 625159-000

Alias ID: 2-1194948-7

Not EU RoHS Compliant

Not EU ELV Compliant

Product Type Wire Splice

Barrel Inside Diameter 1.78 mm [.07 in]

Wire Size (CMA) 320 – 1510

Splice Type SolderSleeve

Overall Length 26.7 mm [1.051 in]

[↓](#) **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

SolderSleeve Conductor Splicing 1.78 (0.070) I.D.

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Wire Splice

Splice Type SolderSleeve

Dimensions

Barrel Inside Diameter 1.78 mm [.07 in]

Wire Size (CMA) 320 – 1510

Overall Length 26.7 mm [1.051 in]

Inside Diameter (Recovered) .64 mm [.025 in]

Usage Conditions

Fluid Resistance Splash Protection

Operating Temperature (Max) (°C) 150

Statement of Compliance

Statement of Compliance

PDF