



[+ TERMINALS & SPLICES](#)

[SPLICES](#)



✓ Active

TE CONNECTIVITY (TE)

D-110-41

Raychem

625160-000

TE Internal Number: 625160-000

Alias ID: 3-1194948-2, 4-25623-3030

Not EU RoHS Compliant

Not EU ELV Compliant

Product Type Wire Splice

Barrel Inside Diameter 2.7 mm [.106 in]

Wire Size (CMA) 608 – 2847

Splice Type SolderSleeve

Overall Length 27.6 mm [1.087 in]

[↓ PRODUCT DRAWING](#)
English

DOCUMENTATION

Product Drawings

SolderSleeve Device

PDF

English

Product Specifications

Product Specification

SolderSleeve Insulated Electrical Termination Devices

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Wire Splice

Splice Type SolderSleeve

Dimensions

Barrel Inside Diameter 2.7 mm [.106 in]

Wire Size (CMA) 608 – 2847

Overall Length 27.6 mm [1.087 in]

Inside Diameter (Recovered) 1.4 mm [.055 in]

Usage Conditions

Fluid Resistance Splash Protection

Operating Temperature (Max) (°C) 150

Statement of Compliance

Statement of Compliance

PDF