



+ TERMINALS & SPLICES

SPLICES



✓ Active

TE CONNECTIVITY (TE)
D-110-0090

Raychem

625372-000

TE Internal Number: 625372-000

Alias ID: 3-1194952-4

Not EU RoHS Compliant

Not EU ELV Compliant

Product Type Wire Splice

Barrel Inside Diameter 7.11 mm [.28 in]

Wire Size (CMA) 8500 – 16200

Splice Type SolderSleeve

Overall Length 54 mm [2.13 in]

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

SolderSleeve Wire Splice 7.11 (0.280) I.D.

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Wire Splice

Splice Type SolderSleeve

Dimensions

Barrel Inside Diameter 7.11 mm [.28 in]

Wire Size (CMA) 8500 – 16200

Overall Length 54 mm [2.13 in]

Inside Diameter (Recovered) 3.56 mm [.14 in]

Usage Conditions

Fluid Resistance Splash Protection

Operating Temperature (Max) (°C) 150

Statement of Compliance

Statement of Compliance

PDF