




+ WIRE AND CABLE

HIGH SPEED DIGITAL & DATA CABLE



✓ Active

TE CONNECTIVITY (TE)

7522B7331-0

7522B7331-0

TE Internal Number: EG4699-000

EU RoHS Compliant

EU ELV Compliant

Cable Type Cheminax

Impedance (Ω) 75

Wire Size (AWG) 22

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

Cheminax, 75 Ohm, AWG 22, 19 Strands Of AWG 34, Twinaxial Cable

PDF

English

Product Specifications

Product Specification

Cable, High-Frequency And Controlled Electrical

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Cheminax

Product Type Cable

Cable Style Round Braided

Product Classification Cable - Coaxial

Electrical Characteristics

Impedance (Ω) 75

Capacitance (pF/ft) 30

Signal Characteristics

Velocity of Propagation 66%

Body Features

Conductor Material Tin-Plated Copper

Jacket Color Black

Jacket Material Thermorad S

Shield Style Single

Shield Material Tin-Plated Copper

Dimensions

Wire Size (AWG) 22

Wire Diameter .81 mm [.032 in]

Dielectric Diameter 1.52 mm [.06 in]

Overall Outside Diameter 4.19 mm [.165 in]

Wire Size (mm²) .3255

Statement of Compliance

Statement of Compliance

PDF
