



2-1194896-8 Product Details

[Share](#) | [Print](#) | [Email](#)


✓ Active

Shield Terminators

ST63-1-00

2-1194896-8 (ST63-1-00)

TE Internal Number: 619819-000

Product Highlights [View All](#)

- Shield Terminator
- Terminator Type = Solder Sleeve
- Fluid Resistance = Immersion
- Cable Temperature Rating = 125 °C
- Jacket Outer Diameter = 1.90 mm

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#)

[Features](#)

[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features		Industry Standards	
Product Type	Shield Terminator	Government/Industry Qualification	No
Termination Features		RoHS/ELV Compliance	Not ELV/RoHS compliant
Terminator Type	Solder Sleeve	Lead Free Solder Processes	Not relevant for lead free process
Dimensions		MIL or NAS Specification (MIL-S-83519) (NAS 1747)	NAS-1747
Shield O.D. (Min.) (mm [in])	0.90 [0.035]	Environmental	
Length (Max.) (mm [in])	16.50 [0.650]	Fluid Resistance	Immersion
Body Features		Operating Temperature (Max.) (°C)	150
Jacket Outer Diameter (mm [in])	1.90 [0.075]	Conditions for Usage	
Configuration Features		Cable Temperature Rating (°C)	125
Preinstalled Lead	Without	Other	
Temperature Indication System	With	Brand	Raychem
Temperature Indication System Type	Fusible Ring		

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

