



| PART NO. | DIA. "A" REF. | MAX. BUNDLE DIA. | WALL "B" REF. | "C" REF. | STANDARD LENGTHS | INSTALLATION TOOL NO. | MATERIAL |
|-------------|---------------|------------------|---------------|----------------|--------------------|-----------------------|--|
| SHR-08-6NB | 0 | .24 (6) | .032 (0.8) | .39 (10) | 328 ft. (100 m) | CAT-05-PP | FLAME RETARDANT NYLON UL94 V-0 RMS-95, |
| | .31 (8) | .39 (10) | .032 (0.8) | .39 (10) | 328 ft. (100 m) | CAT-08-PP | |
| SHR-15-6NB | .59 (15) | .63 (16) | .032 (0.8) | .55 (14) | 164 ft. (50 m) | CAT-15-PP | |
| SHR-20-6NB | .79 (20) | .90 (23) | .035 (0.9) | .67 (17) | 98 ft. (30 m) | CAT-20-PP | |
| SHR-25-6NB | .98 (25) | .98 (25) | .039 (1.0) | .79 (20) | 65 ft. (20 m) | CAT-25-PP | |
| SHR-32-6NB | 1.25 (32) | 1.25 (32) | .050 (1.3) | .980 (24.9) | 49 ft. (15 m) | CAT-32-PP | |
| SHR-05-PPB | .20 (5) | .24 (6) | .032 (0.8) | .39 (10) | 328 ft. (100 m) | CAT-05-PP | |
| SHR-08-PPB | .31 (8) | .39 (10) | .032 (0.8) | .39 (10) | 328 ft. (100 m) | CAT-08-PP | |
| SHR-15-PPB | .59 (15) | .63 (16) | .032 (0.8) | .55 (14) | 164 ft. (50 m) | CAT-15-PP | |
| SHR-20-PPB | .79 (20) | .90 (23) | .035 (0.9) | .67 (17) | 98 ft. (30 m) | CAT-20-PP | |
| SHR-25-PPB | .98 (25) | .98 (25) | .039 (1.0) | .79 (20) | 65 ft. (20 m) | CAT-25-PP | |
| SHR-32-PPB | 1.25 (32) | 1.25 (32) | .050 (1.3) | .980 (24.9) | 49 ft. (15 m) | CAT-32-PP | |
| SHR-05-6VOB | .20 (5) | .24 (6) | .032 (0.8) | .39 (10) | 328 ft. (100 m) | CAT-05-PP | |
| SHR-08-6VOB | .31 (8) | .39 (10) | .032 (0.8) | .39 (10) | 328 ft. (100 m) | CAT-08-PP | |
| SHR-15-6VOB | .59 (15) | .63 (16) | .032 (0.8) | .55 (14) | 164 ft. (50 m) | CAT-15-PP | |
| SHR-20-6VOB | .79 (20) | .90 (23) | .035 (0.9) | .67 (17) | 98 ft. (30 m) | CAT-20-PP | |
| SHR-25-6VOB | .98 (25) | .98 (25) | .039 (1.0) | .79 (20) | 65 ft. (20 m) | CAT-25-PP | |
| SHR-32-6VOB | 1.25 (32) | 1.25 (32) | .050 (1.3) | .980 (24.9) | 49 ft. (15 m) | CAT-32-PP | |

1. MATERIAL: HEAT STABILIZED NYLON 6 (RMS-157) AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER, USE PART NO. SHR-XX-HTNB
2. STANDARD COLOR: BLACK.
OTHER COLORS AVAILABLE BY SPECIAL ORDER.

| | | | | | | | | | |
|-----|-----------------------------|-------------|--------------------------|------------------|-------------------------------|------|-----------|---------------|------------|
| N | SEE CO 200219 FOR CHANGES | SK 07.21.08 | TITLE: SLIT HARNESS WRAP | | | | | DWG IN IN(mm) | |
| K | SEE EC | | TOLERANCES UNLESS NOTED | FILE # SHR | DWN: J.B. | APP: | | PRELIMINARY | |
| J | SEE ECN #825 FOR CHANGES | SM 07.14.04 | .XX=±.020 | MAT'L: SEE NOTES | DT: 01-05-97 | DT: | | PART # | PRINT TYPE |
| I | SEE ECN #619 FOR CHANGES | SM 05.01.03 | .XXX=±.015 | RE: RICHCO INC | RICHCO INC. | | SEE CHART | | CA |
| - | SEE ENGINEERING FOR REV A-H | - | FRAC=1/64 | | PO BOX 804238, CHICAGO, 60680 | | | | |
| REV | DESCRIPTION | ENGR DATE | ANG=1° | | (773) 539-4060 | | | | |