


NYLON 6/6 (RMS-01) COLOR: NATURAL	FLAME RETARDANT (RMS-19) COLOR: NATURAL	"A" ±.015 (±0.4)
SCBS-4-01	SCBS-4-19	1/4 (6.4)
SCBS-6-01	SCBS-6-19	3/8 (9.5)
SCBS-8-01	SCBS-8-19	1/2 (12.7)
SCBS-10-01	SCBS-10-19	5/8 (15.9)
SCBS-12-01	SCBS-12-19	3/4 (19.1)
SCBS-14-01	SCBS-14-19	7/8 (22.2)
SCBS-16-01	SCBS-16-19	1 (25.4)
SCBS-18-01	SCBS-18-19	1-1/8 (28.6)
SCBS-22.5-01	SCBS-22.5-19	1-13/32 (35.7)



TITLE: STUDDED CIRCUIT BOARD SUPPORT				⊕	▭	DWG IN IN (MM)	QR
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°		FILE # SCBS	DWN: PB/JB	APP:		FINAL	
C SEE ECN #512 FOR CHANGES SM 11.08.02		MAT'L: SEE TABLE	DT: 10-02-95	DT:		PART #	
B CHANGED FILE NO. AND TITLE BLOCK SM 05.04.01		RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		SEE TABLE		PRINT TYPE CA
A CONVERTED TO ACAD PB 05.19.95							
REV DESCRIPTION ENGR DATE							

C	SEE ECN #512 FOR CHANGES	SM 11.08.02
B	CHANGED FILE NO. AND TITLE BLOCK	SM 05.04.01
A	CONVERTED TO ACAD	PB 05.19.95
REV	DESCRIPTION	ENGR DATE