


TO PRESS FIT IN A  
 $.312 \pm .003$  (7.9 ± 0.08)  
 DIA. HOLE, IN A  $.25$  (6.4)  
 MIN. PANEL THICKNESS



PART NO.	"A"	"B" BUNDLE DIA. RANGE	"C" REF.
BHKL350-4-01	1/4 (6.4)	.30 - .40 (7.6 - 10.2)	1.0 (25.4)
*BHKL350-6-01	3/8 (9.5)		
*BHKL350-8-01	1/2 (12.7)		
BHKL350-10-01	5/8 (15.9)	.40 - .50 (10.2 - 12.7)	1-1/8 (28.6)
BHKL450-4-01	1/4 (6.4)		
BHKL450-6-01	3/8 (9.5)		
BHKL450-8-01	1/2 (12.7)	.70 - .80 (17.8 - 20.3)	1-1/2 (38.1)
BHKL450-10-01	5/8 (15.9)		
BHKL750-4-01	1/4 (6.4)		
BHKL750-6-01	3/8 (9.5)		
BHKL750-8-01	1/2 (12.7)		
BHKL750-10-01	5/8 (15.9)		

\*PARTS AVAILABLE BY SPECIAL ORDER ONLY

NOTES:

- MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).  
 NYLON 6/ UL 94 V-0 (RMS-19).  
 AVAILABLE BY SPECIAL ORDER.
- COLOR: NATURAL.

TITLE: BLIND HOLE KURLY-LOK			DWG IN IN (MM)		FINAL	
F	SEE ECN #1262 FOR CHANGES	SK 12.11.06	FILE #	BHKL	DWN: P.B.	APP:
E	SEE ECN #914 FOR CHANGES	SK 01.14.05	MAT'L:	SEE NOTES	DT: 07-11-95	DT:
D	SEE ECN #818 FOR CHANGES	SM 10.01.04	RE:	RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060	
C	CHANGED FILE NUMBER	SM 05.31.01			PART #	PRINT TYPE
B	MAT'L RMS-19 ADDED	J.L. 12.18.97			SEE TABLE	CA
A	"C" DIM'S CHANGED; CONV. TO ACAD	PB 07.11.95				
REV	DESCRIPTION	ENGR DATE				