

Search by SKU, Product Name or Keyword

SEARCH

CART

Product Information

Contact Us



MORE CHOICE



FREE SAMPLES



SHIPS TODAY



Home > Fiber, Wire & Cable Manage... > Cable Ties & Mounts > Cable Ties > Standard Cable Ties >



Standard Cable Tie, Nylon, Black, 5.6 in Long, 18 lbs, UL94 V-2

● In Stock

Item Code: CT005B

This Non-Releasable Cable Tie is made of Black Nylon 6/6. It's 5.590 in (142 mm) long and .100 in (2.5 mm) wide

Description	Quantity	Options
Head Type : Non-Releasable	<input type="text" value="100"/>	<div style="background-color: red; color: white; padding: 5px; text-align: center; margin-bottom: 5px;">Add to Cart</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Free Sample</div> <div style="background-color: #ccc; padding: 5px; text-align: center;">Request Quote</div>
Overall Length : 5.590 in (142 mm)		
Overall Width : .100 in (2.5 mm)		
Hole Type : No Screw Hole		
Releasability : Non Releasable		
Material : Nylon		
Coating : Uncoated		
Material Flammability Standard : UL94 V-2		
Color : Black		
Tooth Material : Nylon		
Full Material : Nylon 6/6		
Cable Bundle Diameter Range : 1.38 in (35.1 mm)		
Minimum Loop Tensile Strength : 18 lbs (8.2 kg)		
Certification : UL		
Specifications/Standards (All) : UL		

Downloads



Print Page

Recently Viewed



Standard Cable Tie,
Nylon, Black, 5.6 in Long,
18 lbs, UL94 V-2

Abrasives & Grinding
 Access Hardware
 Adhesives, Sealants & Tapes
 Bearings & Power Transmissions
 Caps & Plugs

Clamps & Workholdings
 Cutting & Machining
 Extrusions & Structural Systems
 Fasteners
 Feet, Casters & Glides

Fiber, Wire & Cable Management
 Flange Protection
 Knobs, Handles & Grips
 Material Handling
 Shop Supplies

PCB & Electronics Hardware
 Pneumatics & Hydraulics
 Raw Materials
 Tamper Evident & Security Seals
 Tooling & Positioning Components
 Tools & Precision Instruments



About Us

About Essentra Components
 About Essentra PLC
 Locations
 Knowledge Center

Customer Service

Contact Us
 Catalogs
 Sample Program
 Free CAD
 Careers
 Distributor Portal

Policies

Privacy Policy
 Terms and Conditions of Sale
 Terms and Conditions of
 Purchase
 Environmental Policy
 Health and Safety
 Quality Statement

Terms of Use

Website Terms of Use
 Cookie Policy

