



Diaphragm Grommet - 16.0 mm | 0.63 in ; 11.0 mm | 0.433 in ; 1

Item code: **DG-19426**

● In production

This diaphragm grommet is used as a blanking plug to conceal access holes until wires are installed. To install wires, pierce the central membrane film and insert wire.



Order sample:

[Add sample +](#)

[Download CAD](#)

[Print page !\[\]\(4b7a79268f6ba26c1471d4232fffa85a_img.jpg\)](#)

Need a quote?

For large volumes and customized products, add to your cart and click request a quote, or email salestoronto@essentracomponents.com and we will respond in 24 hours or next business day

Can't find what you're looking for? Tell us what you are looking for...

Send us your inquiry and we'll get back to you in 24 hours.

[Contact us](#)

[Request a quote](#)

Specifications

Imperial Metric

| | |
|--------------------------|--------------------|
| Compatible Hole Diameter | 0.63 in |
| Inside Diameter | 0.433 in |
| Overall Diameter | 0.748 in |
| Overall Height | 0.228 in |
| Panel Thickness | 0.059 in |
| Colour | Black |
| Full Material | Polyvinyl Chloride |
| Material | PVC |

Type

1

Brand

Richco

Useful Information

Documents



[Material-Data-Sheet-Flexible-PVC-025](#)

Recommended Products



Open Grommet - ;

[See our selection →](#)



Open Grommet -

[See our selection →](#)



**Grommet Strip -
Unserrated ; 6.4 mm |
0.250 in**

[See our selection →](#)



**Stepped Grommet
Black ; 5.0 - 7.0 mm
0.197 - 0.276 in**

[See our selection →](#)

Recently viewed items



**Diaphragm Grommet -
16.0 mm | 0.63 in ; 11.0
mm | 0.433 in ; 1**

[See our selection →](#)



[BACK TO TOP ^](#)

Information Legal Policies

[Contact Us](#)

[About Us](#)

[Sustainability](#)

[Distributor Portal](#)

[Catalogs](#)

[Careers](#)

[Quality Statement](#)

[Conditions of Sale](#)

[Privacy Policy](#)

[Health and Safety](#)

[Modern Slavery](#)

[Statement](#)

Legal Policies

[Terms of Use](#)

[Cookie Policy](#)

[Promotion Terms](#)

[Terms of Purchase](#)

Contact Us

Tel: +1 800 847 0486

Email:
salestoronto@essentracomponents.com



