



Die Cast Fixed Straight Arm Crank Handle: 3.250 in Arm Height, 90° Radius

Item code: ACH-50


● 5 In stock

Aluminium Revolving Die Cast Fixed Straight Arm Crank Handle has a 90° radius and Square Hole mount for use in machinery and commercial product construction.



[Need a quote?](#)

[Request a quote](#) [Login to download CAD](#) [Contact us](#)



Update preview

The preview does not represent the part configuration anymore. You have to generate a new preview.

Specifications

Imperial Metric

Brand	J.W. Winco Inc.
Arm Height	3.250 in
Body Diameter	1.26 in
Body Height	1.34 in
Handle Length	4.92 in

Colour	Natural
Radius	90°
Handle Material	Aluminium
Handle Style	Revolving
Material	Aluminium
Mount Type	Square Hole

Useful Information

Certificates



JW Winco REACH

Recently viewed items



**Fixed Crank Handle;
Square Hole, Revolving,
Aluminum**

[See our selection →](#)

[BACK TO TOP](#) ^

Information

[Contact Us](#)
[About Us](#)
[Careers](#)

Legal Policies

[Cookie Policy](#)
[Privacy Policy](#)
[Terms of Use](#)
[Terms of Purchase](#)
[Terms of Sale](#)

Legal Policies

[Promotion Terms & Conditions](#)
[Health and Safety](#)
[Quality Statement](#)
[GDPR Commitment Statement](#)
[Modern Slavery Statement](#)

Contact Us

Tel: 1(800) 253-0421 

