



Nylon Crossed Pan Machine Screw - Thread Size M4 X .7; Thread Length 25.0 mm | 0.984 in; Head Diameter 7.6-8.0 mm | NaN in

Item code: 50M040070P025 ● 2000 In stock

This crossed pan head screw is made from natural Nylon, is fully threaded and can be used in a wide range of industries and applications. Parts refer to N FE 25-121 for guidance purpose only. Replaces Item No.(s): SPXM4L25A



[See all specs and customize](#) ↓

Print page

Pricing and options

Standard pack: 1000
Order in multiple of 1000

Need a quote?
For large volumes and customized products, add to your cart and click request a quote, or email sales@essentracomponents.com and we will respond within 2 working days.

Specifications

Imperial Metric

Thread Length	0.984 in
Thread Size	M4 X .7
Color	Natural
Material	Nylon
Full Material	Nylon 6/6
Screw Type	Machine Screw
Drive Type	Crossed
Head Type	Pan

Information

[Contact Us](#)

[About Us](#)

[Sustainability](#)

[Distributor Portal](#)

[Catalogs](#)

[Careers](#)

Legal Policies

[Quality Statement](#)

[Conditions of Sale](#)

[Privacy Policy](#)

[Health and Safety](#)

Legal Policies

[Terms of Use](#)

[Cookie Policy](#)

[Promotion Terms](#)

[Terms of Purchase](#)

Contact Us

Tel: +1 800 847 0486 



[Sitemap](#) | Copyright © Essentra plc 2019