



Cable Clamp - Fir Tree Mount, Hinged Locking Top, 9.9 mm

● In Stock

Item Code: HLCC-2BK

This black hinged locking clamp securely holds corrugated/convoluted tubing or other bundles. It has an internal rib spanning the diameter of the clamp providing a tight grip. The outside holding diameter is .39 in. They snap into a .264 in (6.7 mm) diameter hole in a .031 - .118 in (0.8 - 3 mm) panel thickness.

Description	Quantity	Options
Material Flammability Standard : UL94 V-2	<input type="text" value="1000"/>	<div style="background-color: red; color: white; padding: 5px; text-align: center; margin-bottom: 5px;">Add to Cart</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Request CAD</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin-bottom: 5px;">Free Sample</div> <div style="background-color: #ccc; padding: 5px; text-align: center;">Request Quote</div>
Compatible Hole Diameter : .264 in (6.7 mm)		
Compatible Panel Thickness Range : .031 - .118 in (0.8 - 3 mm)		
Brand : Richco		
Operating Temperature Range : -40 - 257 °F (-40 - 125 °C)		
Compatible Cable Diameter Range : .39 in (9.9 mm)		

Downloads



Print Page

Recently Viewed



Cable Clamp - Fir Tree Mount, Hinged Locking Top, 9.9 mm

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding

Clamps & Workholdings

Fiber, Wire & Cable Management PCB & Electronics Hardware

Access Hardware

Cutting & Machining

Flange Protection

Pneumatics & Hydraulics

Adhesives, Sealants & Tapes

Extrusions & Structural Systems Knobs, Handles & Grips

Raw Materials

Bearings & Power Transmissions Fasteners

Material Handling

Tamper Evident & Security Seals

Caps & Plugs

Feet, Casters & Glides

Shop Supplies

Tooling & Positioning Components

Tools & Precision Instruments

[About Us](#)

[Customer Service](#)[Policies](#)

[Terms of Use](#)

[About Essentra Components](#)[Contact Us](#)

[Privacy Policy](#)

[Website Terms of Use](#)

[About Essentra PLC](#)

[Catalogs](#)

[Terms and Conditions of Sale](#)

[Cookie Policy](#)

[Locations](#)

[Sample Program](#) [Terms and Conditions of Purchase](#)

[Knowledge Center](#)

[Free CAD](#)

[Environmental Policy](#)

[Careers](#)

[Health and Safety](#)

[Distributor Portal](#) [Quality Statement](#)



ABOUT SSL CERTIFICATES