



0845 758 5070

United Kingdom

English

Login or Register

ESSENTRA

Search by Part Number, Product Name or Keyword

SEARCH

BASKET




Products Order Catalogue Knowledge Centre Contact Us

Home

Fasteners

Rivets

Push-In Rivets



Mounting Buttons, Black, Nylon 6/6, 3.22 mm Max Hole, 2.0 mm - 2.5 mm Panel

In Stock

Item Code: MMB-125-01BK

Mounting Buttons, Black, Nylon 6/6, 3.22 mm Max Hole, 2.0 mm - 2.5 mm Panel

Description	Quantity	Options
Compatible Hole Diameter	: 3.2 mm	<input type="text" value="1"/>
Head Diameter	: 6.9 mm	Add to Basket
Head Height	: 1.0 mm	View CAD
Anchor Length	: 8.4 mm	Order Sample
Colour	: Black	Request Quote
Material	: Nylon	
Full Material	: Nylon 6/6	
Operating Temperature Range	: -40 to 85 °C	
Brand	: Richco	
ID - Barcode	: 5052751820692	
Compatible Hole Diameter Range	: 3.10 - 3.22 mm	
Compatible Panel Thickness Range	: 2.0 - 2.5 mm	
Material Flammability Standard	: UL94 V-2	

Downloads



Print Page

Dependent Products



Mounting Buttons, Black, Nylon 6/6, 3.22 mm Max Hole, 2.0 mm - 2.5 mm Panel

Access Hardware

Adhesives, Sealants & Tapes

Bearings & Power Transmissions

Caps & Plugs

Clamps & Workholdings

Cutting & Machining

Fasteners

Feet, Casters & Glides

Fibre, Wire & Cable Management

Flange Protection

Furniture, Retail Display & Wipes

Knobs, Handles & Grips

Packaging & Material Handling

PCB & Electronics Hardware

Pneumatics & Hydraulics

Tamper Evident & Security Seals

Tooling & Positioning Components

Tools & Precision Instruments



ABOUT SSL CERTIFICATES



[About Us](#) [Contact Us](#) [Policies](#) [Cookie Policy](#) [Terms of Use](#)

Copyright © Essentra plc 2014