

Search by SKU, Product Name or Keyword

[Products](#) [Contact Us](#) [Catalogs](#) [Sample Program](#) [Free CAD](#)

[Home](#) > [Fasteners](#) > [Rivets](#) > [Push-In Rivets](#)




Fir Tree Rivet, Natural, .20 in Stem Length, .19 in Head Dia., .132 in Hole Dia., Type 6

● In Stock

Item Code: MPLE-32M/35M-01

Natural Nylon 6/6 fir tree rivets. These Rivets have a .19 in head diameter, are compatible with a .132 in hole and have a maximum panel thickness of .073 in



Description	Quantity	Options
Compatible Hole Diameter	<input type="text" value="1000"/>	<input type="button" value="Add to Cart"/> <input type="button" value="Free Sample"/> <input type="button" value="Request Quote"/>
Head Diameter	: .19 in (4.8 mm)	
Head Height	: .04 in (1 mm)	
Anchor Length	: .20 in (5.1 mm)	
Operating Temperature Range	: -40 - 185 °F (-40 - 85 °C)	
Brand	: Richco	
Compatible Panel Thickness Range	: .079 - .073 in (2 - 1.9 mm)	
Series	: MPLE	
Material Flammability Standard	: UL94 V-2	
Type	: 6	

Downloads

Print Page

Products you might be interested in



Fir Tree Rivet, Natural, .20 in Stem Length, .19 in Head Dia., .132 in Hole Dia., Type 6

ESSENTIAL SOLUTIONS DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments

About Us

- [About Essentra Components](#)
- [About Essentra PLC](#)
- [Locations](#)

Customer Service

- [Contact Us](#)
- [Catalogs](#)
- [Sample Program](#)
- [Free CAD](#)
- [Careers](#)
- [Distributor Portal](#)

Policies

- [Privacy Policy](#)
- [Terms and Conditions of Sale](#)
- [Terms and Conditions of](#)
- [Purchase](#)
- [Environmental Policy](#)
- [Health and Safety](#)
- [Quality Statement](#)

Terms of Use

- [Website Terms of Use](#)
- [Cookie Policy](#)



ABOUT SSL CERTIFICATES