



ESSENTRA

Search by SKU, Product Name or Keyword

SEARCH

CART



[Products](#) [Catalogs](#) [Free Samples](#) [Free CAD](#) [Knowledge Center](#) [Contact Us](#)

[Home](#) > [PCB & Electronics Hardware](#) > [Spacers & Standoffs](#) > [Male To Female Standoff](#) >



Threaded Nylon/Brass Spacer, Natural, #8-32, 2.500" Spacer

In Stock

Item Code: TN6-40-832-2

These low voltage insulating standoffs are made of Nylon with Brass inserts for use where high mechanical strength is required. They have #8-32 threads with a 2.500 in Spacer length.

Downloads



Print Page

Dependent Products

Recently Viewed



Threaded Nylon/Brass
Spacer, Natural, #8-32,
2.500" Spacer

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments



About Us

[About Essentra Components](#)
[About Essentra PLC](#)
[Locations](#)
[Knowledge Center](#)

Customer Service

[Contact Us](#)
[Catalogs](#)
[Sample Program](#)
[Free CAD](#)
[Careers](#)
[Distributor Portal](#)

Policies

[Privacy Policy](#)
[Terms and Conditions of Sale](#)
[Terms and Conditions of Purchase](#)
[Environmental Policy](#)
[Health and Safety](#)
[Quality Statement](#)

Terms of Use

[Website Terms of Use](#)
[Cookie Policy](#)



ABOUT SSL CERTIFICATES

