

Search by SKU, Product Name or Keyword

SEARCH

CART



[Products](#) [Catalogs](#) [Free Samples](#) [Free CAD](#) [Knowledge Center](#) [Contact Us](#)

Home > Feet, Casters & Glides > Bumper Feet > Self Adhesive Bumpers & R...



Square Self Adhesive Bumper & Rubber Foot: Black, Base Diameter, .25 in (6.4 mm) Base Height

● In Stock !

Item Code: RBS-29BK

PU Square Self Adhesive Bumper withstands temperatures from 32 - 122 °F (0 - 50 °C). The Polyurethane diameter rubber foot protects surfaces.



Description	Quantity	Options																						
<table border="0"> <tr><td>Shape (All)</td><td>: Square</td></tr> <tr><td>Color</td><td>: Black</td></tr> <tr><td>Base Length</td><td>: .78 in (19.8 mm)</td></tr> <tr><td>Base Width</td><td>: .78 in (19.8 mm)</td></tr> <tr><td>Full Material</td><td>: Polyurethane</td></tr> <tr><td>Operating Temperature Range</td><td>: 32 - 122 °F (0 - 50 °C)</td></tr> <tr><td>Material Flammability Standard</td><td>: UL94 HB</td></tr> <tr><td>Material</td><td>: PU</td></tr> <tr><td>Brand</td><td>: Richco</td></tr> <tr><td>Base Height</td><td>: .25 in (6.4 mm)</td></tr> <tr><td>Base Diameter</td><td>: .780 in (19.8 mm)</td></tr> </table>	Shape (All)	: Square	Color	: Black	Base Length	: .78 in (19.8 mm)	Base Width	: .78 in (19.8 mm)	Full Material	: Polyurethane	Operating Temperature Range	: 32 - 122 °F (0 - 50 °C)	Material Flammability Standard	: UL94 HB	Material	: PU	Brand	: Richco	Base Height	: .25 in (6.4 mm)	Base Diameter	: .780 in (19.8 mm)	<input type="text" value="98"/> <div style="background-color: red; color: white; padding: 5px; text-align: center; margin: 5px 0;">Add to Cart</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Request CAD</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Free Sample</div> <div style="background-color: #ccc; padding: 5px; text-align: center; margin: 5px 0;">Request Quote</div>	
Shape (All)	: Square																							
Color	: Black																							
Base Length	: .78 in (19.8 mm)																							
Base Width	: .78 in (19.8 mm)																							
Full Material	: Polyurethane																							
Operating Temperature Range	: 32 - 122 °F (0 - 50 °C)																							
Material Flammability Standard	: UL94 HB																							
Material	: PU																							
Brand	: Richco																							
Base Height	: .25 in (6.4 mm)																							
Base Diameter	: .780 in (19.8 mm)																							

Downloads ▼



Print Page

Recently Viewed



Square Self Adhesive Bumper & Rubber Foot: Black, Base Diameter, .25 in (6.4 mm) Base Height

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments



[About Us](#)

[About Essentra Components](#)
[About Essentra PLC](#)

[Customer Service](#)

[Contact Us](#)
[Catalogs](#)

[Policies](#)

[Privacy Policy](#)
[Terms and Conditions of Sale](#)

[Terms of Use](#)

[Website Terms of Use](#)
[Cookie Policy](#)

[ABOUT SSL CERTIFICATES](#)

[Locations](#)
[Knowledge Center](#)

[Sample Program](#)
[Free CAD](#)
[Careers](#)
[Distributor Portal](#)

[Terms and Conditions of
Purchase](#)
[Environmental Policy](#)
[Health and Safety](#)
[Quality Statement](#)