

Search by SKU, Product Name or Keyword

SEARCH

CART



[Products](#) [Catalogs](#) [Free Samples](#) [Free CAD](#) [Knowledge Center](#) [Contact Us](#)

Home > PCB & Electronics Hardware > Supports > Reverse Locking Supports



Reverse Mount Support, Push/Flat Top, .187 in Hole/.062 in Panel, .438 in Spacer

● In Stock !

Item Code: RLCBSRS-7-01

This is a push spacer with a flat top to hold heavy boards. The bottom hole is .187 in diameter with a .062 in maximum panel thickness. It has a .438 in spacer length and is made from Natural UL94 V-2 Nylon 6/6.



Description	Quantity	Options																										
<table border="0"> <tr><td>Hole A Fix Type</td><td>: Flat</td></tr> <tr><td>Hole B Fix Type</td><td>: Snap Lock</td></tr> <tr><td>Style</td><td>: 1</td></tr> <tr><td>Spacer Length</td><td>: .438 in (11.1 mm)</td></tr> <tr><td>Color</td><td>: Natural</td></tr> <tr><td>Full Material</td><td>: Nylon 6/6</td></tr> <tr><td>Material Flammability Standard</td><td>: UL94 V-2</td></tr> <tr><td>Hole Diameter A</td><td>: 4.4 mm (0.173 in)</td></tr> <tr><td>Hole Diameter B</td><td>: .187 in (4.7 mm)</td></tr> <tr><td>Operating Temperature Range</td><td>: -40 - 185 °F (-40 - 85 °C)</td></tr> <tr><td>Brand</td><td>: Richco</td></tr> <tr><td>Material</td><td>: Nylon</td></tr> <tr><td>Panel Thickness B Range</td><td>: .059 - .062 in (1.5 - 1.6 mm)</td></tr> </table>	Hole A Fix Type	: Flat	Hole B Fix Type	: Snap Lock	Style	: 1	Spacer Length	: .438 in (11.1 mm)	Color	: Natural	Full Material	: Nylon 6/6	Material Flammability Standard	: UL94 V-2	Hole Diameter A	: 4.4 mm (0.173 in)	Hole Diameter B	: .187 in (4.7 mm)	Operating Temperature Range	: -40 - 185 °F (-40 - 85 °C)	Brand	: Richco	Material	: Nylon	Panel Thickness B Range	: .059 - .062 in (1.5 - 1.6 mm)	<input type="text" value="1000"/> <div style="background-color: red; color: white; text-align: center; padding: 5px; margin: 5px 0;">Add to Cart</div> <div style="background-color: #ccc; text-align: center; padding: 5px; margin: 5px 0;">Free Sample</div> <div style="background-color: #ccc; text-align: center; padding: 5px; margin: 5px 0;">Request Quote</div>	
Hole A Fix Type	: Flat																											
Hole B Fix Type	: Snap Lock																											
Style	: 1																											
Spacer Length	: .438 in (11.1 mm)																											
Color	: Natural																											
Full Material	: Nylon 6/6																											
Material Flammability Standard	: UL94 V-2																											
Hole Diameter A	: 4.4 mm (0.173 in)																											
Hole Diameter B	: .187 in (4.7 mm)																											
Operating Temperature Range	: -40 - 185 °F (-40 - 85 °C)																											
Brand	: Richco																											
Material	: Nylon																											
Panel Thickness B Range	: .059 - .062 in (1.5 - 1.6 mm)																											

Downloads ▼



Print Page

Recently Viewed



Reverse Mount Support, Push/Flat Top, .187 in Hole/.062 in Panel, .438 in Spacer

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments



[About Essentra Components](#)
[About Essentra PLC](#)
[Locations](#)
[Knowledge Center](#)

[Contact Us](#)
[Catalogs](#)
[Sample Program](#)
[Free CAD](#)
[Careers](#)
[Distributor Portal](#)

[Privacy Policy](#)
[Terms and Conditions of Sale](#)
[Terms and Conditions of Purchase](#)
[Environmental Policy](#)
[Health and Safety](#)
[Quality Statement](#)

[Website Terms of Use](#)
[Cookie Policy](#)

ABOUT SSL CERTIFICATES