



ESSENTRA

Search by SKU, Product Name or Keyword

SEARCH

CART



[Quick Order](#) [Products](#) [Contact Us](#) [Catalogs](#) [Sample Program](#) [Free CAD](#)

[Home](#) > [PCB & Electronics Hardware](#) > [Spacers & Standoffs](#) > [Non Threaded Spacer](#)



Shoulder Washer, Natural,.115 in ID,.031 in Flange Length,#4

Item Code: IW030A

Washer is made from Nylon and has a base outside diameter of .145 in (3.7 mm) and a base height of .031 in (0.8 mm).

● In Stock
Free sample available

Description	Quantity	Options																		
<table border="0"> <tr> <td>Inside Diameter</td> <td>: .115 in (2.9 mm)</td> </tr> <tr> <td>Base Height</td> <td>: .031 in (0.8 mm)</td> </tr> <tr> <td>Base Outside Diameter</td> <td>: .145 in (3.7 mm)</td> </tr> <tr> <td>Color</td> <td>: Natural</td> </tr> <tr> <td>Compatible Screw Sizes (All)</td> <td>: #4, M2.5</td> </tr> <tr> <td>Flange Height</td> <td>: .046 in (1.2 mm)</td> </tr> <tr> <td>Flange Outside Diameter</td> <td>: .235 in (6 mm)</td> </tr> <tr> <td>Material</td> <td>: Nylon</td> </tr> <tr> <td>Full Material</td> <td>: Nylon</td> </tr> </table>	Inside Diameter	: .115 in (2.9 mm)	Base Height	: .031 in (0.8 mm)	Base Outside Diameter	: .145 in (3.7 mm)	Color	: Natural	Compatible Screw Sizes (All)	: #4, M2.5	Flange Height	: .046 in (1.2 mm)	Flange Outside Diameter	: .235 in (6 mm)	Material	: Nylon	Full Material	: Nylon	<input type="text" value="1000"/> <div style="background-color: red; color: white; text-align: center; padding: 5px; margin: 5px 0;">Add to Cart</div> <div style="background-color: #ccc; text-align: center; padding: 5px; margin: 5px 0;">Request CAD</div> <div style="background-color: #ccc; text-align: center; padding: 5px; margin: 5px 0;">Free Sample</div> <div style="background-color: #ccc; text-align: center; padding: 5px; margin: 5px 0;">Request Quote</div>	
Inside Diameter	: .115 in (2.9 mm)																			
Base Height	: .031 in (0.8 mm)																			
Base Outside Diameter	: .145 in (3.7 mm)																			
Color	: Natural																			
Compatible Screw Sizes (All)	: #4, M2.5																			
Flange Height	: .046 in (1.2 mm)																			
Flange Outside Diameter	: .235 in (6 mm)																			
Material	: Nylon																			
Full Material	: Nylon																			



Print Page

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments



About Us

[About Essentra Components](#)
[About Essentra PLC](#)
[Locations](#)

Customer Service

[Contact Us](#)
[Catalogs](#)
[Sample Program](#)
[Free CAD](#)
[Careers](#)
[Distributor Portal](#)

Policies

[Privacy Policy](#)
[Terms and Conditions of Sale](#)
[Terms and Conditions of Purchase](#)
[Environmental Policy](#)
[Health and Safety](#)
[Quality Statement](#)

Terms of Use

[Website Terms of Use](#)
[Cookie Policy](#)

