


PART NO.	"A" ±1/8" (±3.2)	"W" ±.125 (±3.2)	"L" ±.50 (±12.7)	PACKAGING
RKW-6-6	3/8 (9.5)	.75 (19.1)	6.0 (152.4)	100
RKW-8-6	1/2 (12.7)	1.0 (25.4)		
RKW-8-8				
RKW-8-11				
RKW-12-15			15.0 (381.0)	
RKW-12-18	3/4 (19.1)	1.5 (38.1)	18.0 (457.2)	
RKW-12-24			24.0 (609.6)	



NOTES:

1. MATERIAL: HOOK: LOW DENSITY POLYETHYLENE (RMS-249).
2. LOOP: NYLON KNIT (RMS-251).
3. OPERATING TEMP: 120°F.

TO ORDER COLORS ADD SUFFIX TO "PART NO."
 BLACK: -BK, WHITE: -W, BLUE: -BL,
 RED: -RD, YELLOW: -YL,
 GREEN: -GN, ORANGE -OR.

OTHER COLORS AVAILABLE BY
 SPECIAL ORDER.

G	SEE CO 200601 FOR CHANGES	SK 11.30.10	TITLE: RICHCO KWIK WRAP			DWG IN IN (MM)	FINAL	PRINT TYPE CA
F	SEE ECN #1263 FOR CHANGES	SK 12.12.06						
E	SEE ECN #538 FOR CHANGES	SM 12.10.02	FILE # RKW			DWN: J.L.	APP:	PART # SEE TABLE
D	REMOVED RKS-8-12 TO SAPARATE PRINT	SM 02.26.02	MAT'L: SEE NOTES			DT: 6.2.98	DT:	
C	METRIC CONVERSION CORRECTED	DM 12.12.01	RE: RICHCO, INC.			RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		
B	CHANGED FILE NO.	DM 12.06.01	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1'					
A	CHANGED TABLE; ADDED 2 BASE PARTS & DIM "W".	SM 02.23.01						
REV	DESCRIPTION	ENGR DATE						