

REV.	MODIFICATION.	DATE	DRN
01	PRODUCTION RELEASE	19/03/12	SF




FIG 1






FIG 2



NOTE:
ALTERNATE UNITS FOR REFERENCE ONLY

PART No	FIG	'A'	CABLE BUNDLE MAX
SCC-SE-4-19	1	4[0.157]	9[0.354]
SCCBH-SE-4-19	2		
SCC-SE-8-19	1	8[0.315]	
SCCBH-SE-8-19	2		
SCC-SE-10-19	1	10[0.393]	
SCCBH-SE-10-19	2		
SCC-SE-12-19	1	12[0.472]	
SCCBH-SE-12-19	2		

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

RICHCO, INC. WWW.RICHCO-INC.COM		ALL DIMENSIONS IN mm GENERAL TOLERANCES ±0.25 UNLESS OTHERWISE STATED 1 DECIMAL PLACE ±0.25 2 DECIMAL PLACES ±0.10 ANGULAR ±1°	THIRD ANGLE
MATERIAL: NYLON 6/6 UL94-V0 (RMS-19)		COLOUR: NATURAL	
DESCRIPTION: STANDOFF CABLE CLIP SIDE ENTRY		PART No: SEE TABLE	
DRG No: 012-018		PROJECT NUMBER: EU12-0011	
DRN RA		DATE 29/2/12	CHKD TC
DATE 23/03/12		SCALE NTS	SHEET No. 1 OF 1