



Contact Us: 800-847-0486

Country / Language

Login / Register

Cart Total: \$0.00

Search By Keyword or Part Number

- Products ▾
- Quick Order
- Knowledge Center
- Order Catalog
- Contact Us
- My Account

- Home >
- Feet, Casters & Glides >
- Adjustable Leveling Feet & Accessories >
- Adjustable Leveling Feet



Stud Mount Leveling Feet - Metal Swivel Base

In Stock

SKU: TL-5SS

Stainless Steel Stud Type Leveling Pad

ECID: 1093508

- Base Diameter (Imperial): 4.000 in
- Base Diameter (Metric): 101.6 mm
- Base Height (Imperial): 1.875 in
- Base Height (Metric): 47.63 mm
- Base Material: Stainless Steel
- Bolt Down Base: Regular
- Maximum Static Load Capacity (Imperial): 22000 lbs
- Maximum Static Load Capacity (Metric): 97860.88 N
- Mount Type: Threaded Stud
- Mounting Type: Threaded Stud
- Swivel Articulation: 15°
- Thread Full Material: 303 Stainless Steel
- Thread Length (Imperial): 4.250 in
- Thread Length (Metric): 107.95 mm
- Thread Material: Stainless Steel
- Thread Size: 1-8

Quantity Price Each
1

Standard Pack: 1

-
-
-
-

- Customer Service
- Contact Us
- Knowledge Center
- My Account
- Order A Catalog

- About Us
- Overview
- Careers
- Distribution Sites
- Free CAD Library
- Free Samples

- Important Info
- Privacy Policy
- Terms Of Purchase/Sale/Use
- Press Releases
- Minimum Order

Sign up for news and offers