

Pushbutton, 18.2 mm, screw terminal, momentary contact function, 2 NO, bezel black



fields of application

- > Mechanical and system engineering
- > Model construction
- > Home technology



description

Pushbutton with mounting hole diameter 18.2 mm, non-illuminated, 250 V / 4 A

technical data

> general

illuminated	No
Bezel color	black
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
Packaging	Box
Packaging unit	100 pcs.
net weight	16 g
Operating life	50,000 Cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 IP65 with sealing cap
RoHS compliant	Yes
REACH compliant	Yes

> mounting diameters

Mounting hole	18.2 mm
Mounting depth	34 mm

direct links

- > [RAFI eCatalog](#)

Installation height	10.5 mm
Outside dimension, width	22 mm
> mechanical data	
Actuation function	momentary contact function
Operating force, min.	9.5 N
Operating travel, max.	5 mm
Contact function	2 NO
Contact system	Bridge-sliding contact
Contact material	Silver
Fixing	Threaded ring
Terminal on the rear	Screw terminal
> electrical data	
Rated voltage, max.	250 V
Rated current, max.	2 A