

## RAFIX 22 QR, switching element, cage clamp terminal, silver, with coupling, for BA9s, 1 NO



### fields of application

- > Measurement-control-regulation
- > Electrical engineering
- > Mechanical and system engineering
- > Vehicle construction



### description

### technical data

#### > general

illuminated	Yes
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
Lamp socket	BA9s
Vibration-resistance according to standard IEC 60068-2-6	5 g at 10 - 500 Hz
Packaging unit	10 pcs.
Environment resistance	IEC 60068-2-14 IEC 60068-2-30 IEC 60068-2-33 IEC 60068-2-78
RoHS compliant	Yes
REACH compliant	Yes

#### > mounting diameters

Mounting depth	56.4 mm
Outside dimension, length	49.9 mm
Outside dimension, width	39.5 mm
Outside dimension, height	30 mm

#### > mechanical data

Contact function	1 NO
Contact system	Bridge contact
Fixing	Latching

#### direct links

- > [RAFI eCatalog](#)

**drawings**

**System drawing**

