

Pushbutton, 16.2 mm, momentary contact function, 1 NO, bezel red



fields of application

- > Mechanical and system engineering
- > Model construction
- > Home technology

description

Pushbutton with mounting hole diameter 16.2 mm, screw terminal, non-illuminated, 250 V / 4 A

technical data

> general

illuminated	No
Bezel color	red
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
Packaging	Box
Packaging unit	100 pcs.
net weight	11 g
Operating life	150,000 Cycles
Degree of protection, front side, according to DIN EN 60529	IP40 IP65 IP65 with sealing cap
RoHS compliant	Yes
REACH compliant	Yes

> mounting diameters

Mounting hole	16.2 mm
Mounting depth	41 mm
Installation height	9 mm
Outside dimension, width	20 mm

> mechanical data

Actuation function	momentary contact function
Operating force, min.	7,5 N
Operating travel, max.	4.3 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver

direct links

- > [RAFI eCatalog](#)

Fixing

Threaded ring

Terminal on the rear

Screw terminal

> electrical data

Rated voltage, max.

250 V

Rated current, max.

2 A

drawings

Dimensioned drawing

