

**RAFIX 22 FSR - Keylock switch, latching, 1 x 90°, L shape****1.30.285.221/0100****General information**

Color of front ring	black
Form of collar	round

**Dimensions**

Dimensions of collar	ø 31.3 mm
Overall height	45.1 mm
Mounting hole	22.3 mm
Key grid	35 x 35 mm

**Mechanical design**

Mounting	ring nut
Contact function	latching
Wafers	5
Illuminability	no
Lock type	001
Main key	on request
Rotating angle	1 x 90°, L shape
Key removal position	0+1
Torque for nut ring	1.2 Nm

**Mechanical characteristics**

Torque max.	1.3 Nm
-------------	--------

**Other specifications**

Degree of protection from front side	IP65 (DIN EN 60529)
Ambient temp. operating min.	-40 °C
Ambient temp. operating max.	+85 °C
Storage temperature min.	-40 °C
Storage temperature max.	+85 °C
Environmental resistance	acc. to IEC 60068-2-14, -30, -33 and -78
Salt spray	IEC 600 68-2-11
ROHS compliant	yes
REACH compliant	yes

## Panel cut-out to IEC 60947-5-1

