

KD-M8/7A



Description

The diode module is equipped with 7 diodes. The anodes of the diodes are all connected to each other. The module is used for failure indication systems (lamp tests).

- common anode
- Connection with screw-type terminals

Technical Data

General Data

Cut-off voltage	1000 V
Input / voltage	250 V AC/DC
Forward current	1 A
Forward voltage	1.1 V at 1 A
Total current through all diodes Σ I _{diodes} (V x n x I _V)	less than or equal to 1.8 A 1.2 x 0.5 x 0.001111
Weight	20 g
Operating temperature range	-10 °C to +50 °C
Storage temperature range	-25 °C to +70 °C
Ingress protection for housing / terminal block	IP40 / IP20

[Check US distributor inventory](#)
[Part number](#)
[Downloads](#)
[Find contact person](#)
[Inquiry](#)
[Show part in ePLAN data portal](#)


PRODUCTS

[P|Cabling](#)
[U|Contact](#)
[C|Logline](#)

COMPANY

[About METZ CONNECT](#)
[METZ CONNECT Worldwide](#)
[News](#)
[Fairs and Events](#)

SERVICE

[Catalogs | Brochures](#)
[Downloads](#)
[Newsletter](#)
[General Terms and Conditions](#)

**WE
REALIZE
IDEAS**

METZ CONNECT GmbH

The use of cookies allows us to optimize your experience on this website. In addition to technically necessary cookies, we use cookies for statistical purposes and for quality assurance (Google Analytics and Google Maps). You can find further information in our data protection notice.

[Only accept necessary cookies](#) [Individual settings ...](#) [Accept all cookies](#)