



DIN Cable Mount

Male and female cord plug with shielded barrel or insulated snaplock plastic body. Two piece metal barrel surrounds pin insert to form an electrical shield. The entire insert assembly is held together by snapping the insulated plastic shell over the assembly. The barrel's special metal tab locks the shell in place. Standard color of plastic shell is gray. All-purpose cable clamp.

[enlarge](#)

Products

Specifications

[Need more info? Contact Switchcraft customer service](#)

Product	Description	Typical Mating	Layout	Drawings	Distributor Inventory
03BL2M	DIN Cable Mount Connector, male cord plug with ground key-rib, 2 pins with insulated switch actuator		Pin Arrangements 1		check stock
05BL3MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 3 pins at 180°		Pin Arrangements 2		check stock
05BL5MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 5 pins at 180°		Pin Arrangements 5		check stock
05DL5MX	DIN Cable Mount Connector, right angle male plug, black strain relief, 5 pins at 180°		Pin Arrangements 5		check stock
05GM3MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 3 pins at 180°, gray body and strain relief		Pin Arrangements 2		check stock
05GM5MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 5 pins at 180°, Gray body and strain relief		Pin Arrangements 5		check stock
06AL5FX	DIN Cable Mount Connector, female receptacle with ground contact, 5 contacts at 180°		Contact Arrangements F		check stock
09BL4MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 4 pins at 210°		Pin Arrangements 3		check stock
09GM4MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 4 pins at 210°, Gray body and strain relief		Pin Arrangements 3		check stock
12BL5MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 5 pins at 240°		Pin Arrangements 4		check stock
12BL6MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 6 pins at 240°		Pin Arrangements 6		check stock
12DL5M	DIN Cable Mount Connector, right angle male plug, black strain relief, 5 pins at 240°		Pin Arrangements 4		check stock
12DL6M	DIN Cable Mount Connector, right angle male plug, black strain relief, 6 pins at 240°		Pin Arrangements 6		check stock
12GM5MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 5 pins at 240°, Gray body and strain relief		Pin Arrangements 4		check stock
12GM6MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 6 pins at 240°, Gray body and strain relief		Pin Arrangements 6		check stock
13AL5F	DIN Cable Mount Connector, female receptacle with ground contact, 5 contacts at 240°		Contact Arrangements E		check stock
13AL6F	DIN Cable Mount Connector, female receptacle with ground contact, 5 contacts at 240°		Contact Arrangements G		check stock
15AL7F	DIN Cable Mount Connector, female receptacle with ground contact, 7 contacts at 270°		Contact Arrangements H		check stock
15AL8FX	DIN Cable Mount Connector, female receptacle with ground contact, 8 contacts at 270°		Contact Arrangements N		check stock
15BL7M	DIN Cable Mount Connector, male cord plug with ground key-rib, 7 pins at 270°		Pin Arrangements 7		check stock
15BL8MX	DIN Cable Mount Connector, male cord plug with ground key-rib, 7 pins at 270°		Pin Arrangements 8		check stock
15GM7MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 7 pins at 270°, Gray body and strain relief		Pin Arrangements 7		check stock
15GM8MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 8 pins at 270°, Gray body and strain relief		Pin Arrangements 9		check stock
20BL8M	DIN Connector Receptacle				check stock
20GM8MX	DIN Cable Mount Connector, male cord plug with shielded barrel, 8 pins at 262°, Gray body and strain relief		Pin Arrangements 10		check stock

denotes a special order