



**RECOMMENDED
PANEL CUT-OUT**

CUSTOMER DRAWING

NOTES:

1. INSERTION LOSS: 1.0 dB MAX.
2. MATERIALS:
HOUSING - DELRIN, BLACK
TOSLINK ADAPTER - ABS
CENTER PIN - BRASS, GOLD PLATED
DUST CAPS - PVC
3. FOR SCREWS TO BE SHIPPED WITH ASSEMBLY AND INDIVIDUAL PACKAGING, ADD SUFFIX -PKG TO PART NUMBER.
4. WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-POUNDS MAXIMUM.
5. THIS PRODUCT IS RoHS COMPLIANT.

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
					SIZE	WIDTH	MULT	LBS/M	TEMPER		
					UNLESS OTHERWISE SPECIFIED			SEE NOTES			
					1. ALL DIMENSIONS IN INCHES			MATERIAL			
					- TWO PLACE DECIMALS ±0.02			SPEC No.			
					- THREE PLACE DECIMALS ±0.005			SPEC No.			
B	26950	5-7-12	TO	TJK	FIRST USED ON			SCALE 3:2			
A	26347	2/26/09	RS	TJK	DATE DRAWN	BY	CHKD	APVD	Switchcraft®		
REV	ECO NUMBER	DATE	BY	APVD	5/12/08	JGK	RS	TJK			
REVISIONS					DO NOT SCALE DRAWING					SHEET 1 OF 1	
					E SERIES TOSLINK ADAPTER, RoHS					PART No. EHTL2	
										REV B	

