


SPECIFICATIONS
 MATERIALS: □
 Nylon □
 -4°F to 176 °F
 (-20°C to 80°C)




PART NUMBER	MALE THREAD A	FEMALE THREAD B	WRENCHING FLATS W	THREAD LENGTH T	HEIGHT H
AF-1207-BK	M12 x 1.5	PG 7	.67 (17)	.31 (8)	.47 (12)
AF-2013-BK	M20 x 1.5	PG 13.5	.98 (25)	.31 (8)	.51 (13)
AF-2516-BK	M25 x 1.5	PG 16	1.14 (29)	.31 (8)	.55 (14)
AF-3221-BK	M32 x 1.5	PG 21	1.43 (36)	.39 (10)	.59 (15)
AF-4029-BK	M40 x 1.5	PG 29	1.77 (45)	.39 (10)	.59 (15)
AF-5036-BK	M50 x 1.5	PG 36	2.16 (55)	.47 (12)	.67 (17)
AP-0916-BK	PG 9	M16 x 1,5	.83 (21)	.31 (8)	.47 (12)
AP-1320-BK	PG 13.5	M20 x 1,5	.98 (25)	.31 (8)	.51 (13)
AP-1620-BK	PG 16	M20 x 1,5	1.06 (27)	.31 (8)	.51 (13)
AP-1625-BK	PG 16	M25 x 1,5	1.18 (30)	.31 (8)	.59 (15)
AP-2132-BK	PG 21	M32 x 1,5	1.46 (37)	.31 (8)	.59 (15)
AP-2940-BK	PG 29	M40 x 1,5	1.77 (45)	.39 (10)	.67 (17)

NOTES:

- 1) GENERAL DIMENSIONS DRAWINGS.
- 2) DIMENSIONS [] ARE IN MILLIMETER.
- 3) DIMENSIONS NOTED ARE FOR REFERENCE ONLY.

Third angle projection



14853 E HINDSDALE AVE, SUITE D
 CENTENNIAL, CO 80112-4240, USA
 TEL: +1-303-699-1135
 TOLL FREE: +1-800-456-9012
 E MAIL: info@sealconusa.com,
 WEBSITE: www.sealconusa.com

