





SIRIUS Signal Columns

8WD44










Selection and ordering data

Diameter 70 mm, thermoplastic enclosure, degree of protection IP 65

	Version	Color	8WD44 signal. columns		8WD44 signal. columns		8WD44 signal. columns		Weight approx. kg	
			Order No.	List Price \$ 1 unit	Order No.	List Price \$ 1 unit	Order No.	List Price \$ 1 unit		
 <p>8WD44 00-1A.</p>	Lamp: Base BA 15d, 5 W, 24 V/ 115 V/230 V (not included in the scope of supply)									
	• Steady-light element		Rated voltage UC 12 to 230 V						0.1	
		red	8WD44 00-1AB	49.00						
		green	8WD44 00-1AC	49.00						
		yellow	8WD44 00-1AD	49.00						
		clear	8WD44 00-1AE	49.00						
		blue	8WD44 00-1AF	49.00						
			Rated voltage UC 24 V		Rated voltage AC 115 V		Rated voltage AC 230V			
	• Repeated-flash light element		red	8WD44 20-1BB	113.00	8WD44 40-1BB	113.00	8WD44 50-1BB	113.00	0.1
			green	8WD44 20-1BC	113.00	8WD44 40-1BC	113.00	8WD44 50-1BC	113.00	
		yellow	8WD44 20-1BD	113.00	8WD44 40-1BD	113.00	8WD44 50-1BD	113.00		
		clear	8WD44 20-1BE	113.00	8WD44 40-1BE	113.00	8WD44 50-1BE	113.00		
		blue	8WD44 20-1BF	113.00	8WD44 40-1BF	113.00	8WD44 50-1BF	113.00		
 <p>8WD44 20-5AB</p>	• Steady-light element LED		red	8WD44 20-5AB	160.00	8WD44 40-5AB	160.00	8WD44 50-5AB	160.00	0.1
			green	8WD44 20-5AC	160.00	8WD44 40-5AC	160.00	8WD44 50-5AC	160.00	
			yellow	8WD44 20-5AD	160.00	8WD44 40-5AD	160.00	8WD44 50-5AD	160.00	
			clear	8WD44 20-5AE	160.00	8WD44 40-5AE	160.00	8WD44 50-5AE	160.00	
			blue	8WD44 20-5AF	160.00	8WD44 40-5AF	160.00	8WD44 50-5AF	160.00	
	• Repeated-flash light element LED		red	8WD44 20-5BB	175.00	–	–	–	–	
			green	8WD44 20-5BC	175.00	–	–	–	–	
			yellow	8WD44 20-5BD	175.00	–	–	–	–	
	• Rotating-beacon element LED		red	8WD44 20-5DB	193.00	–	–	–	–	
			green	8WD44 20-5DC	193.00	–	–	–	–	
		yellow	8WD44 20-5DD	193.00	–	–	–	–		
 <p>8WD44 20-0FA</p>	• Buzzer element ¹⁾ 85 dB Tone adjustable: pulsating or continuous		8WD44 20-0FA	200.00	8WD44 40-0FA	200.00	8WD44 50-0FA	200.00	0.1	
	• Siren element ¹⁾		Rated voltage DC 24 V							
			- 108 dB, IP 40	8WD44 20-0EA	100.00	–	–	–	0.1	
			- Multi-tone siren, 100 dB, 8 tones and amplification can be set	8WD44 20-0EA2	160.00	8WD44 40-0EA2	160.00	8WD44 50-0EA2	160.00	0.1
 <p>8WD44 08-0AA, 8WD44 08-0AD</p>	• Screw terminals		Connection element incl. cover						0.1	
			- for mounting on pipes	8WD44 08-0AA	49.00					
			- for mounting on bracket or floor	8WD44 08-0AB	49.00					
	• With Cage Clamp		- for mounting on pipes	8WD44 08-0AD	49.00				0.1	
		- for mounting on bracket or floor	8WD44 08-0AE	49.00						

1) Operation necessitate top position mounting on column.

Accessories

Design	Rated voltage	Order No.	List Price \$ 1 unit	Weight approx. kg	Pack
 <p>Foot with pipe (100 mm) Foot, single</p>	Plastic foot with pipe	8WD43 08-0DA ^①	49.00	0.1	
	Plastic for mounting on pipes	8WD43 08-0DB ^②	12.80	0.05	
	Cast-iron foot for pipe mounting > 400 mm	8WD43 08-0DC ^③	28.00		
 <p>Connecting socket for foot</p>	Side cable outlet	8WD43 08-0DD ^④	19.30	0.2	
	Side cable outlet, with magnetic base ¹⁾	8WD43 08-0DE ^⑤	126.00	0.4	
	1/2" NPT Adapter	8WD43 08-0DF	16.00		
 <p>Pipe, single</p>	100 mm	8WD42 08-0EF	16.70	0.03	
	150 mm	8WD43 08-0EE	45.00	0.05	
	250 mm	8WD43 08-0EA	19.30	0.1	
	400 mm	8WD43 08-0EB	28.00	0.2	
	1000 mm	8WD43 08-0ED	66.00	0.4	
 <p>8WD43 08-0CA Bracket for wall mounting</p> <ul style="list-style-type: none"> • for single-sided mounting • for double-sided mounting 		8WD43 08-0CA	20.50	0.1	
		8WD43 08-0CB	20.50		
 <p>8WD44 28-0BA AS-Interface adapter element ²⁾</p>	4 signalling elements up to 200 mA max. are possible	24 V	8WD44 28-0BA	225.00	0.1
	4 signalling elements up to 1.5 A max. are possible	24 V	8WD44 28-0BB	250.00	
 <p>8WD43 58-1XX Lamps</p>	Base BA 15d, 5 W	24 V 115 V 230 V	8WD43 28-1XX 8WD43 48-1XX 8WD43 58-1XX	6.40 6.40 6.40	0.01
	 <p>LEDs</p>	red green yellow clear blue	24 V UC	8WD44 28-6XB	90.00
				8WD44 28-6XC	90.00
				8WD44 28-6XD	90.00
8WD44 28-6XE				90.00	
red green yellow clear blue		AC 115 V	8WD44 48-6XB	90.00	
			8WD44 48-6XC	90.00	
			8WD44 48-6XD	90.00	
			8WD44 48-6XE	90.00	
red green yellow clear blue		AC 230 V	8WD44 58-6XB	90.00	
			8WD44 58-6XC	90.00	
			8WD44 58-6XD	90.00	
			8WD44 58-6XE	90.00	
 <p>Bracket for pipe mounting</p>		8WD44 08-0CC	21.00		
	 <p>Bracket for floor mounting</p>		8WD44 08-0CD	21.00	

1) For horizontal mounting, only 1 element is recommended.
2) Operation necessitate mounting as the lowest element on signal column.