



SETRON, cylindrical fuse link, 10 x 38 mm, 12 A, gG, Un AC: 500 V

Model		
product brand name	SETRON	
product designation	Cylindrical fuse link	
General technical data		
operating class of the fuse link	gG	
size of the fuse link	10x38 mm	
type of voltage / of the operating voltage	AC	
operating voltage / rated value	500 V	
Dissipation		
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.4 W	
operational current / at AC / rated value	12 A	
Main circuit		
operational current / rated value	12 A	
Product details		
product component / striker	No	
Mechanical Design		
mounting position	Any, preferably vertical	
net weight	8 g	
<b>General Product Approval</b>	<b>Declaration of Conformity</b>	<b>Test Certificates</b>



[Miscellaneous](#)

**Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6006-1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW6006-1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW6006-1](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6006-1)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

