

6XV18782A | 6XV18782A



Industrial Ethernet FastConnect TP standard cable GP 4x 2, TP installation CAT6A cable for connection to IE FC RJ45 plug 4x 2, AWG24, sold by the meter, delivery length max. 2000 m Minimum order 20m

List Price [Show prices](#)

Customer Price [Show prices](#)

DataSheet in PDF [Download](#)

Service & Support (Manuals, Certificates, FAQs...) [Download](#)

Image gallery and data for M-CAD and E-CAD (1) (1)

Accessory (13)



[Show all](#)

Product data Further Product Information

Product

Article Number (Market Facing Number) [6XV18782A](#) | 6XV18782A

Product Description Industrial Ethernet FastConnect TP standard cable GP 4x 2, TP installation CAT6A cable for connection to IE FC RJ45 plug 4x 2, AWG24, sold by the meter, delivery length max. 2000 m Minimum order 20m

Product family [IE FC TP cable 4 x 2](#)

Product Lifecycle (PLM) PM300:Active Product

Price data

Price Group 675

List Price [Show prices](#)

Customer Price [Show prices](#)

Metal Factor None

Delivery information

Export Control Regulations AL : N / ECCN : N

Standard lead time ex-works 3 Day/Days

Net Weight (lb) 0.168 lb

Packaging Dimension 0.039 x 0.039 x 0.039

Package size unit of measure Inch

Quantity Unit 1 Meter

Packaging Quantity 1

Additional Product Information

EAN 4019169853378

UPC 040892552607

Commodity Code 85444920

LKZ_FDB/ CatalogID IK

Product Group 2427

Group Code R320

Country of origin Germany

Compliance with the substance restrictions according to RoHS directive Given

Returnable Yes

WEEE (2012/19/EU) Take-Back Obligation Yes

REACH Art. 33 Duty to inform according to the current list of candidates [Lead CAS-No. 7439-92-1 > 0, 1 % \(w / w\)](#)

Classifications

	Version	Classification
eClass	6	27-06-18-01
eClass	7.1	27-06-18-01
eClass	8	27-06-18-01
eClass	9	27-06-18-01
eClass	9.1	27-06-18-01
ETIM	5	EC000830
ETIM	6	EC000830
ETIM	7	EC003249
IDEA	4	1722
UNSPSC	14	26-12-16-09
UNSPSC	15	26-12-16-09